



MMP-060S/3H



Product code

[ex : 30° hood / White / NORDIC type / Narrow 11° / 3000K]

MMP-060S/3H/W/1N/N/10A 30/N1/2

Basic Product Series

Hood

Color

Track type

Light distribution

Light source

Color temperature

Driver type

Auth-entification

○NORDIC type

Dimming | Non-dimming

White MMP-060S/3H/W/1N/N.M/10A24.27.30.35.40/N1/2

Matte black MMP-060S/3H/M/1N/N.M/10A24.27.30.35.40/N1/2

Silver MMP-060S/3H/S/1N/N.M/10A24.27.30.35.40/N1/2



W : White


M : Matte black

S : Silver

Products Specifications

- Input Voltage AC120V
- Power consumption 15.4W(AC120V)
- Luminance flux 941 ~ 1,088 lm
- Color rendering CRI (Ra)=93(typ)
- Fixture's weight 0.84 lbs
- Light distribution Narrow (11°) Medium (19°)
- Input current 0.129A (120V)
- Aiming distance 0.1m (3 15/16 in)
- Tilting angle 100°
- Filter lighting® 2 Filters

Size



Track system designation

NORDIC : type TEK-44,48,412
NORDIC ALUMINIUM INC

- This fixture is compatible with 2-circuit track only. The fixture attaches to both the left and right circuit rails of the track. Please ensure that only one power feed is supplied to the track.

Additional Accesaries

• Lens Filter

Full-Diffuser lens filter

MLA-060/DF01



[data download](#)

Semi-Diffuser lens filter

MLA-060/DS01



[data download](#)

Full-spread lens filter

MLA-060/SF01



[data download](#)

Semi-Spread lens filter

MLA-060/SS01



[data download](#)

Edge-control lens filter

MLA-060/EC01



[data download](#)


Sharpeners lens filter

MLA-060/SH01



[data download](#)

Installation




- ① Pull down the cover guard.
- ② Rotate the gear lever.

- ③ Push the driver box against the lighting rail.
- ④ Rotate the gear lever and lock it.
- ⑤ Push up the cover guard.

How to do tilt lock / pan lock

Each angle can be locked by allen wrench attached.



Light distribution

Narrow : 11°

N	11°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	828	0.66	941lm	992lm	1042lm
6.56	207	1.31	748	789	828
9.84	92	1.97	187	197	207
13.12	52	2.62	83	88	92
			47	49	52
					53
					54

3000K / 1042Lm

Medium : 19°

M	19°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	493	1.15	941lm	992lm	1042lm
6.56	123	2.30	445	469	493
9.84	55	3.44	111	117	123
13.12	31	4.59	49	52	55
			28	29	31
					31
					32

3000K / 1042Lm

Light distribution with Filter lighting®

Full-Diffuser lens filter | MLA-060/DF01

N	40°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	62	2.43	941lm	992lm	1042lm
6.56	16	4.86	748	789	828
9.84	7	7.28	187	197	207
13.12	4	9.71	83	88	92
			47	49	52
					53
					54

for Narrow

for Narrow 3000K / 1042Lm

for Medium 3000K / 1042Lm

Semi-Diffuser lens filter | MLA-060/DS01

N	33°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	128	1.97	941lm	992lm	1042lm
6.56	32	3.94	445	469	493
9.84	14	5.91	111	117	123
13.12	8	7.87	49	52	55
			28	29	31
					31
					32

for Narrow

for Narrow 3000K / 1042Lm

for Medium 3000K / 1042Lm

Full-spread lens filter | MLA-060/SF01

N	13°/44°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	177	0.79/2.69	941lm	992lm	1042lm
6.56	44	1.57/5.38	748	789	828
9.84	20	2.36/8.07	187	197	207
13.12	11	3.15/10.76	83	88	92
			47	49	52
					53
					54

for Narrow

for Narrow 3000K / 1042Lm

for Medium 3000K / 1042Lm

Semi-Spread lens filter | MLA-060/SS01

N	13°/32°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	305	0.79/1.90	941lm	992lm	1042lm
6.56	76	1.57/3.81	445	469	493
9.84	34	2.36/5.71	111	117	123
13.12	19	3.15/7.61	49	52	55
			28	29	31
					31
					32

for Narrow

for Narrow 3000K / 1042Lm

for Medium 3000K / 1042Lm

Edge-control lens filter | MLA-060/EC01

N	32°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	88	1.94	941lm	992lm	1042lm
6.56	22	3.87	748	789	828
9.84	10	5.81	187	197	207
13.12	6	7.74	83	88	92
			47	49	52
					53
					54

for Narrow

for Narrow 3000K / 1042Lm

for Medium 3000K / 1042Lm

Sharpening lens | MLA-060/SH01

N	9°				
H(ft)	E(ft-cd)	D(ft)	E(ft-cd)	2400K	2700K
3.28	642	0.56	941lm	992lm	1042lm
6.56	160	1.12	445	469	493
9.84	71	1.67	111	117	123
13.12	40	2.23	49	52	55
			28	29	31
					31
					32

for Narrow

for Narrow 3000K / 1042Lm

for Medium 3000K / 1042Lm

The attachment of the filters



- Remove the lock by sliding the body along the arrow direction, and detach the hood from the body.



- Rotate the option holder in the hood along the arrow direction and take the option holder out from the hood.




- Put the filter into the hood.
※ up to 2 filters can be inserted.
※ The sharpening lens are counted as 2 lens.



- Put back the option holder to the hood.



- Match the mark of the hood and the body and rotate the hood to lock.



Contact

Mosheo Corporation

2B Airport Drive Ext. Hopedale, MA 01747

Phone : +1-774-804-3283

E-mail : ModuleXSales@Mosheocorp.com

ModuleX